



**Female connector with snap-in
mounting feet and earth conductor
contact 5 pole with moulded pole
marking switchable**
267-115

ITEM-NO. (ITEM-NO.)	267-115
Cross section1 (Cross section / mm²)	0.5 - 1
Cross section2 (Cross section / AWG)	22 - 18
Strip length (Strip length / mm)	8 - 8
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	6
P (NO. OF POLES)	5
Height (Height / mm)	34
Width (Width / mm)	32
Depth (Depth / mm)	32
COLOR (COLOR)	weiß
WEIGHT (WEIGHT / g)	8.981