



Conductor support with field connection and with snap-in mounting foot 4 pole with direct contact of the earth conductor with standard marking
267-304

ITEM-NO. (ITEM-NO.)	267-304
Cross section1 (Cross section / mm²)	1.5 - 2.5
Cross section2 (Cross section / AWG)	16 - 14
Strip length (Strip length / mm)	11 - 12
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	6
P (NO. OF POLES)	4
Height (Height / mm)	19
Width (Width / mm)	39.1
Depth (Depth / mm)	30.4
COLOR (COLOR)	weiß
WEIGHT (WEIGHT / g)	17.33
Comment (Comment)	N / PE 1 / 2