



<b>ITEM-NO. (ITEM-NO.)</b>	267-315
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	1.5 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	16 - 14
<b>Strip length (Strip length / mm)</b>	11 - 12
<b>Measured voltage (Measured voltage / V)</b>	500
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	6
<b>P (NO. OF POLES)</b>	5
<b>Height (Height / mm)</b>	19
<b>Width (Width / mm)</b>	39.1
<b>Depth (Depth / mm)</b>	30.4
<b>COLOR (COLOR)</b>	weiß
<b>WEIGHT (WEIGHT / g)</b>	20.7
<b>Comment (Comment)</b>	N / PE / 1 / 2 / 3