





**4-CONDUCTOR SENSOR TERMINAL
BLOCK LATERAL MARKING for DIN
35 rail
270-570**

ITEM-NO. (ITEM-NO.)	270-570
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	250
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	18
Height (Height / mm)	39
Width (Width / mm)	5
Depth (Depth / mm)	83
No. of connection Points (No. of connection Points)	5
No. of potentials (No. of potentials)	4
COLOR (COLOR)	grau