





**4-CONDUCTOR SENSOR SUPPLY
TERMINAL BLOCK Internal bridge 9 A
LATERAL MARKING
270-574**

| | |
|---|------------|
| ITEM-NO. (ITEM-NO.) | 270-574 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 6 - 7 |
| Measured voltage (Measured voltage / V) | 250 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 18 |
| Height (Height / mm) | 39 |
| Width (Width / mm) | 5 |
| Depth (Depth / mm) | 83 |
| No. of connection Points (No. of connection Points) | 5 |
| No. of potentials (No. of potentials) | 4 |
| COLOR (COLOR) | orange |