





**Male connector with snap-in mounting  
foot 3 pole with moulded pole marking  
switchable**  
277-123

<b>ITEM-NO. (ITEM-NO.)</b>	277-123
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.5 - 1
<b>Cross section2 (Cross section / AWG)</b>	20 - 18
<b>Strip length (Strip length / mm)</b>	10 - 11
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>P (NO. OF POLES)</b>	3
<b>Height (Height / mm)</b>	35.4
<b>Width (Width / mm)</b>	25
<b>Depth (Depth / mm)</b>	37
<b>COLOR (COLOR)</b>	weiß