





**Female connector without fixing
element 5 pole with moulded pole
marking
277-131**

ITEM-NO. (ITEM-NO.)	277-131
Cross section1 (Cross section / mm²)	1.5 - 2.5
Cross section2 (Cross section / AWG)	16 - 14
Strip length (Strip length / mm)	11 - 12
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
P (NO. OF POLES)	5
Height (Height / mm)	31.4
Width (Width / mm)	30
Depth (Depth / mm)	40
COLOR (COLOR)	weiß