



ITEM-NO. (ITEM-NO.)	279-501
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	18
Height (Height / mm)	39
Width (Width / mm)	4
Depth (Depth / mm)	68
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau
Comment (Comment)	L/L