





**4-CONDUCTOR DIODE TERMINAL  
BLOCK LATERAL MARKING for lamp  
test circuits up to 60 V  
279-620/281-408**

|  |                 |
|--|-----------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                 | 279-620/281-408 |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>     | 0.08 - 1.5      |
| <b>Cross section2 (Cross section / AWG)</b>                | 28 - 16         |
| <b>Strip length (Strip length / mm)</b>                    | 8 - 9           |
| <b>Current intensity (Current intensity / A)</b>           | 0.5             |
| <b>Height (Height / mm)</b>                                | 27              |
| <b>Width (Width / mm)</b>                                  | 4               |
| <b>Depth (Depth / mm)</b>                                  | 68              |
| <b>No. of connection Points (No. of connection Points)</b> | 4               |
| <b>No. of potentials (No. of potentials)</b>               | 1               |
| <b>COLOR (COLOR)</b>                                       | grau            |