



| | |
|--|-----------------|
| ITEM-NO. (ITEM-NO.) | 279-815/281-410 |
| Cross section1 (Cross section / mm²) | 0.08 - 1.5 |
| Cross section2 (Cross section / AWG) | 28 - 16 |
| Strip length (Strip length / mm) | 8 - 9 |
| Current intensity (Current intensity / A) | 0.5 |
| Height (Height / mm) | 27 |
| Width (Width / mm) | 4 |
| Depth (Depth / mm) | 73 |
| No. of connection Points (No. of connection Points) | 4 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | grau |
| Comment (Comment) | Schaltung I |