

## Product Description

For the benefits, refer to SKINTOP® K-M ATEX plus blue



## Application range

- With reducing seal insert, to seal cables with smaller outer diameters.

## Benefits

- For the benefits, refer to SKINTOP® K-M ATEX plus blue

## Design

- Metric connection thread acc. to EN 50262



Technical Data

**Caution**

Refer to the instruction leaflet for the installation dimensions and torques

**Approvals**

IBExU08ATEX 1063 X Ex II 1D Ex tD A20 IP 6x Ex II 2G Ex e II

**Colour delivered**

Blue (RAL 5015)

**Material**

Body: special polyamide Seal: special elastomer O-ring: CR

**Tests**

DIN EN 60079-0 DIN EN 60079-7

**Protection rating**

IP 68 - 10 bar

**Temperature range**

-20°C to +80°C

Article List

Part number	Article designation / size	Clamping range ØF (mm)	Thread M	SW (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINTOP® KR-M ATEX plus blue							
54115405	KR-M 12 ATEX plus blue	2-4	12 x 1.5	15	26,5 - 30	8.0	50
54115415	KR-M 16 ATEX plus blue	4-6	16 x 1.5	19	29 - 34	8.0	50
54115425	KR-M 20 ATEX plus blue	5-10	20 x 1.5	25	34 - 37	9.0	50
54115435	KR-M 25 ATEX plus blue	6-13	25 x 1.5	30	35 - 40	10.0	25
54115445	KR-M 32 ATEX plus blue	9-15	32 x 1.5	36	39 - 47	10.0	25
54115455	KR-M 40 ATEX plus blue	16-23	40 x 1.5	46	43 - 52	10.0	10
54115465	KR-M 50 ATEX plus blue	22-29	50 x 1.5	55	54 - 62	12.0	5
54115475	KR-M 63 ATEX plus blue	29-39	63 x 1.5	66	59 - 71	12.0	5

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.