





**END AND INTERMEDIATE PLATE 2.5  
MM / 0.098 IN THICK**  
280-301

<b>ITEM-NO. (ITEM-NO.)</b>	280-302
<b>Height (Height / mm)</b>	30.5
<b>Width (Width / mm)</b>	2.5
<b>Depth (Depth / mm)</b>	40
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	1.89