



DATA SHEET	53112005
SKINTOP® MS- M-XL/ MSR- M-XL	valid from : 23.04.2008

The SKINTOP® MS-M / MSR-M a nickel-plated brass cable gland with long metric connecting thread which combines high quality with regard to consistency and reliability. This gland is especially designed for use in manufacturing of machines and equipment, in measuring, controlling as well as in the pharmaceutical industry and for medical equipment.



Components:

Gland body	nickel-plated brass
Cap nut	nickel-plated brass
Insert with lamellar design	plastic polyamide-based
Seal insert	elastomere
Sealing ring	elastomere

Technical features:

Connecting thread:	M 12 up to M 50 in acc. to EN 60 423
IP protection:	IP 68 - 5 bar, test in acc. to EN 60 529,
Temperature range:	- 25° C up to + 100° C
Type:	MS-M-XL = standard MSR-M-XL = standard with reducing seal insert

Approvals:



For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M. Schmid	Document: DB53112005_3EN	page 1 of 1
------------------------------------	--------------------------	-------------