



**TRIPLE DECK TERMINAL BLOCK
EARTH/THROUGH/CARRIER FOR
PLUGGABLE FUSE MODULES for DIN
35 rail
280-510**

ITEM-NO. (ITEM-NO.)	280-510
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	20
Height (Height / mm)	49.5
Width (Width / mm)	5
Depth (Depth / mm)	103
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grün-gelb/blau/grau
WEIGHT (WEIGHT / g)	21.5