



ITEM-NO. (ITEM-NO.)	280-537
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	20
Height (Height / mm)	58.5
Width (Width / mm)	5
Depth (Depth / mm)	64
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grün-gelb/blau
WEIGHT (WEIGHT / g)	13.778