





**SENSOR-LED TERMINAL BLOCK  
CENTRE MARKING FOR PNP  
(POSITIVE) SWITCHING SENSORS  
280-560/281-434**

<b>ITEM-NO. (ITEM-NO.)</b>	280-560/281-434
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Current intensity (Current intensity / A)</b>	20
<b>Height (Height / mm)</b>	55.5
<b>Width (Width / mm)</b>	5
<b>Depth (Depth / mm)</b>	80
<b>No. of connection Points (No. of connection Points)</b>	4
<b>No. of potentials (No. of potentials)</b>	3
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	11.02
<b>Comment (Comment)</b>	für PNP (plus)-schaltende Initiatioren