



ITEM-NO. (ITEM-NO.)	280-562/281-411
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	20
RM (PIN SPACING / mm)	
P (NO. OF POLES)	
Height (Height / mm)	55.5
Width (Width / mm)	5
Depth (Depth / mm)	80
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	10.24
Comment (Comment)	
Dimensions (Dimensions)	