

Accessories
DAE M12 PA long**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

General ordering data

Type	DAE M12 PA long
Order No.	1868570000
Version	Compensating element, Polyamide 6, External thread: M 12, IP 66, IP 68, IP 69K
GTIN (EAN)	4032248440429
Qty.	10 pc(s).

**Accessories
DAE M12 PA long**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	17.4 mm	Net weight	1.7 g
--------	---------	------------	-------

General information

AF size 1	17 mm	Air flow	0.8 l/min at 0.1 bar ΔP, up to 7.6 l/min at 1bar ΔP
Cable gland	metric	Colour code	RAL 9005
External thread	M 12	Length of thread	10 mm
Material	Polyamide 6	O-Ring	NBR
Operating temperature range, max.	105 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Torque for connecting adapter, max.	1.5 Nm
Torque for connecting adapter, min.	1.5 Nm	UL 94 flammability rating	V-2
Wasser inlet point	> 1.5 bar		

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09

Product information

Descriptive text ordering data	Light grey version - RAL 7035 - on request
--------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------