



|   |            |
|---|------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 280-618    |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 2.5 |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 14    |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 9      |
| <b>Measured voltage (Measured voltage / V)</b>              | 400        |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 6          |
| <b>Pollution degree (Pollution degree)</b>                  | 3          |
| <b>Current intensity (Current intensity / A)</b>            | 10         |
| <b>Height (Height / mm)</b>                                 | 28         |
| <b>Width (Width / mm)</b>                                   | 12         |
| <b>Depth (Depth / mm)</b>                                   | 50         |
| <b>No. of connection Points (No. of connection Points)</b>  | 2          |
| <b>No. of potentials (No. of potentials)</b>                | 2          |
| <b>COLOR (COLOR)</b>  | grau       |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 11.442     |