



**2-CONDUCTOR DISCONNECT
TERMINAL BLOCK FOR TEST AND
MEASUREMENT with disconnect tab
CENTRE MARKING
280-627**

| | |
|---|------------|
| ITEM-NO. (ITEM-NO.) | 280-627 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 400 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 10 |
| Height (Height / mm) | 52.5 |
| Width (Width / mm) | 5 |
| Depth (Depth / mm) | 50 |
| No. of connection Points (No. of connection Points) | 2 |
| No. of potentials (No. of potentials) | 2 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 9.576 |