





**4-CONDUCTOR LED TERMINAL  
BLOCK CENTRE MARKING WITH RED  
LED**  
280-658/281-413

|  |                 |
|--|-----------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                 | 280-658/281-434 |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>     | 0.08 - 2.5      |
| <b>Cross section2 (Cross section / AWG)</b>                | 28 - 14         |
| <b>Strip length (Strip length / mm)</b>                    | 8 - 9           |
| <b>Height (Height / mm)</b>                                | 28              |
| <b>Width (Width / mm)</b>                                  | 5               |
| <b>Depth (Depth / mm)</b>                                  | 75              |
| <b>No. of connection Points (No. of connection Points)</b> | 4               |
| <b>No. of potentials (No. of potentials)</b>               | 1               |
| <b>COLOR (COLOR)</b>                                       | grau            |
| <b>WEIGHT (WEIGHT / g)</b>                                 | 9.51            |
| <b>Comment (Comment)</b>                                   | Schaltung I     |