



ITEM-NO. (ITEM-NO.)	280-686
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	10
Height (Height / mm)	28
Width (Width / mm)	5
Depth (Depth / mm)	75
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	8.833
RGB (RGB)	0.67,0.67,0.67,0