

**Data sheet | Item number: 280-852/281-414**

Fuse plug; 5 mm wide; with soldered miniature fuse; with additional indicator lamp; red LED; DC 30 - 65 V; 500 mA FF



[www.wago.com/280-852/281-414](http://www.wago.com/280-852/281-414)



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

**Data**

**Electrical data**

**Ratings per IEC/EN 60664-1**

Rated voltage (III / 3)	125 V
Rated current	5 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

## Geometrical Data

Width	5 mm / 0.197 inch
Plug width	5 mm / 0.197 inch

## Mechanical data

Marking level	without marking level
---------------	-----------------------

## Material Data






Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.067 MJ
Weight	2.77 g

## Commercial data

Country of origin	DE
GTIN	4045454362744
Customs Tariff No.	85366990990
Product Group	1 (Rail Mounted Terminal Blocks)

## Compatible products

### clamps

	<b>Item no.: 280-610</b> 3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-610">www.wago.com/280-610</a>
	<b>Item no.: 280-616</b> 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-616">www.wago.com/280-616</a>
	<b>Item no.: 280-686</b> 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-686">www.wago.com/280-686</a>
	<b>Item no.: 280-816</b> 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-816">www.wago.com/280-816</a>
	<b>Item no.: 280-916</b> 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-916">www.wago.com/280-916</a>

Subject to changes.