



**4-CONDUCTOR DISCONNECT  
TERMINAL BLOCK FOR TEST AND  
MEASUREMENT DISCONNECT LINK  
ORANGE WITH TEST SLOT FOR TEST  
PLUG Ø 2 MM/ 0.079 IN AND Ø 2.3 MM  
/ 0.091 IN  
280-874**

<b>ITEM-NO. (ITEM-NO.)</b>	280-874
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	16
<b>Height (Height / mm)</b>	28.5
<b>Width (Width / mm)</b>	5
<b>Depth (Depth / mm)</b>	89
<b>No. of connection Points (No. of connection Points)</b>	4
<b>No. of potentials (No. of potentials)</b>	2
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	12.066