

Data sheet | Item number: 281-407

Test plug; 6 mm wide; Nominal current 24 A; for 0.08 mm² - 2.5 mm²

www.wago.com/281-407



RoHS 
Compliant

BOMcheck.net

Color: **Data****Electrical data****Ratings per IEC/EN 60664-1**

Rated current	24 A
---------------	------

Connection data

Connection technology	CAGE CLAMP®
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 Inch
Total number of connection points	1
Total number of potentials	1
Type of wiring	Front-entry wiring

Geometrical Data

Width	6 mm / 0.236 inch
-------	-------------------

Material Data

Color	gray
Fire load	0.032 MJ
Weight	2.219 g

Commercial data

Country of origin	DE
GTIN	4044918255622
Customs Tariff No.	85366990990
Product Group	1 (Rail Mounted Terminal Blocks)

Downloads**Documentation****Bid Text**

281-407

Oct 12, 2017

DOC

Download



24.1 kB

smartDATA

CAD data

3D Download 281-407

URL

Download

Subject to changes.