



**RAIL-MOUNTED QUADRUPLE DECK
TERMINAL BLOCK** Rail-mounted
terminal blocks for fast electric motor
wiring L1 - L2
281-531

ITEM-NO. (ITEM-NO.)	281-531
Cross section1 (Cross section / mm²)	0.08 - 4
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	20
Height (Height / mm)	62.5
Width (Width / mm)	6
Depth (Depth / mm)	100
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
Comment (Comment)	L1 - L2