



**RAIL-MOUNTED QUADRUPLE DECK  
TERMINAL BLOCK** Rail-mounted  
terminal blocks for fast electric motor  
wiring L1 - L2 - L3  
281-532

<b>ITEM-NO. (ITEM-NO.)</b>	281-532
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 4
<b>Cross section2 (Cross section / AWG)</b>	28 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	20
<b>Height (Height / mm)</b>	62.5
<b>Width (Width / mm)</b>	6
<b>Depth (Depth / mm)</b>	100
<b>No. of connection Points (No. of connection Points)</b>	6
<b>No. of potentials (No. of potentials)</b>	3
<b>COLOR (COLOR)</b>	grau
<b>Comment (Comment)</b>	L1 - L2 - L3