



**FUSED DISCONNECT TERMINAL
BLOCK WITH PIVOTABLE FUSE
HOLDER for miniature metric fuses 5
x 20 mm 230 V
281-611/281-417**

ITEM-NO. (ITEM-NO.)	281-612/281-417
Cross section1 (Cross section / mm²)	0.08 - 4
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	10
Height (Height / mm)	60
Width (Width / mm)	8
Depth (Depth / mm)	60
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	17.67
Comment (Comment)	für G-Sicherungseinsatz 5 x 25 mm