



| | |
|--|-----------------|
| ITEM-NO. (ITEM-NO.) | 281-665/281-401 |
| Cross section1 (Cross section / mm²) | 0.08 - 4 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 9 - 10 |
| Current intensity (Current intensity / A) | 1.5 |
| Height (Height / mm) | 29 |
| Width (Width / mm) | 6 |
| Depth (Depth / mm) | 86 |
| No. of connection Points (No. of connection Points) | 4 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 13.94 |
| Comment (Comment) | Schaltung II |