



**DISCONNECT TERMINAL BLOCK FOR
TEST PURPOSES with touch-proof
test plugs FOR TEST PLUG 4 MM / 0.
157 IN Ø
282-860**

ITEM-NO. (ITEM-NO.)	282-860
Cross section1 (Cross section / mm²)	0.2 - 6
Cross section2 (Cross section / AWG)	24 - 10
Strip length (Strip length / mm)	12 - 13
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	30
Height (Height / mm)	75
Width (Width / mm)	8
Depth (Depth / mm)	122
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	44.678