



**DISCONNECT TERMINAL BLOCK FOR  
TEST PURPOSES with touch-proof  
test plugs FOR TEST PLUG 4 MM / 0.  
157 IN Ø  
282-870**

<b>ITEM-NO. (ITEM-NO.)</b>	282-870
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.2 - 6
<b>Cross section2 (Cross section / AWG)</b>	24 - 10
<b>Strip length (Strip length / mm)</b>	12 - 13
<b>Measured voltage (Measured voltage / V)</b>	500
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	30
<b>Height (Height / mm)</b>	75
<b>Width (Width / mm)</b>	8
<b>Depth (Depth / mm)</b>	122
<b>No. of connection Points (No. of connection Points)</b>	3
<b>No. of potentials (No. of potentials)</b>	2
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	48.221