



<b>ITEM-NO. (ITEM-NO.)</b>	282-993
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.5 - 6
<b>Cross section2 (Cross section / AWG)</b>	20 - 10
<b>Strip length (Strip length / mm)</b>	12 - 13
<b>Measured voltage (Measured voltage / V)</b>	550
<b>Measured shock voltage (Measured shock voltage / kV)</b>	
<b>Pollution degree (Pollution degree)</b>	
<b>Current intensity (Current intensity / A)</b>	39
<b>Height (Height / mm)</b>	32.5
<b>Width (Width / mm)</b>	8
<b>Depth (Depth / mm)</b>	93
<b>No. of connection Points (No. of connection Points)</b>	3
<b>No. of potentials (No. of potentials)</b>	1
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	20.37
<b>Comment (Comment)</b>	für Ex e II-Anwendungen geeignet