





**END AND INTERMEDIATE PLATE 2.5  
MM / 0.098 IN THICK**  
283-325

<b>ITEM-NO. (ITEM-NO.)</b>	283-328
<b>Height (Height / mm)</b>	37.5
<b>Width (Width / mm)</b>	2.5
<b>Depth (Depth / mm)</b>	94.4
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	6.15