





**2-CONDUCTOR EARTH TERMINAL  
BLOCK LATERAL MARKING for DIN  
35 rail  
284-107**

<b>ITEM-NO. (ITEM-NO.)</b>	284-107
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.2 - 10
<b>Cross section2 (Cross section / AWG)</b>	24 - 08
<b>Strip length (Strip length / mm)</b>	12 - 13
<b>Height (Height / mm)</b>	41.5
<b>Width (Width / mm)</b>	10
<b>Depth (Depth / mm)</b>	52
<b>No. of connection Points (No. of connection Points)</b>	2
<b>No. of potentials (No. of potentials)</b>	1
<b>COLOR (COLOR)</b>	grün-gelb
<b>WEIGHT (WEIGHT / g)</b>	27.555