



**DISTRIBUTION TERMINAL BLOCK 3 x
CAGE CLAMP® connection 10 mm² 1
x SCREW-CLAMP CONNECTION 35
MM²/AWG 2
284-621**

| | |
|---|----------|
| ITEM-NO. (ITEM-NO.) | 284-624 |
| Cross section1 (Cross section / mm²) | 0.2 - 10 |
| Cross section2 (Cross section / AWG) | 24 - 08 |
| Strip length (Strip length / mm) | 12 - 14 |
| Measured voltage (Measured voltage / V) | 800 |
| Measured shock voltage (Measured shock voltage / kV) | 8 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 125 |
| Height (Height / mm) | 39.5 |
| Width (Width / mm) | 17.5 |
| Depth (Depth / mm) | 89 |
| No. of connection Points (No. of connection Points) | 4 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | blau |
| WEIGHT (WEIGHT / g) | 55.6 |