



| | |
|---|---------|
| ITEM-NO. (ITEM-NO.) | 285-604 |
| Cross section1 (Cross section / mm²) | 6 - 35 |
| Cross section2 (Cross section / AWG) | 8 - 02 |
| Strip length (Strip length / mm) | 23 - 23 |
| Measured voltage (Measured voltage / V) | 800 |
| Measured shock voltage (Measured shock voltage / kV) | 8 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 125 |
| Height (Height / mm) | 52.5 |
| Width (Width / mm) | 16 |
| Depth (Depth / mm) | 115.5 |
| No. of connection Points (No. of connection Points) | 2 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | blau |
| WEIGHT (WEIGHT / g) | 131.446 |
| Comment (Comment) | |