



|  |                                  |
|--|----------------------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                 | 285-637/999-950                  |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>     | 6 - 35                           |
| <b>Cross section2 (Cross section / AWG)</b>                | 8 - 02                           |
| <b>Strip length (Strip length / mm)</b>                    | 23 - 23                          |
| <b>Height (Height / mm)</b>                                | 53                               |
| <b>Width (Width / mm)</b>                                  | 26                               |
| <b>Depth (Depth / mm)</b>                                  | 100                              |
| <b>No. of connection Points (No. of connection Points)</b> | 2                                |
| <b>No. of potentials (No. of potentials)</b>               | 1                                |
| <b>COLOR (COLOR)</b>                                       | grün-gelb                        |
| <b>WEIGHT (WEIGHT / g)</b>                                 | 107.395                          |
| <b>Comment (Comment)</b>                                   | Für Ex e II-Anwendungen geeignet |