



ITEM-NO. (ITEM-NO.)	285-691
Cross section1 (Cross section / mm²)	6 - 35
Cross section2 (Cross section / AWG)	8 - 02
Strip length (Strip length / mm)	23 - 23
Measured voltage (Measured voltage / V)	750
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	120
Height (Height / mm)	52.5
Width (Width / mm)	16
Depth (Depth / mm)	115.5
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	131.446
Comment (Comment)	für Ex e II-Anwendungen geeignet