





**Lighting Connector without ground  
contact 2 pole with snap-in mounting  
feet**  
294-5002

<b>ITEM-NO. (ITEM-NO.)</b>	294-5002
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	2 x 0.5 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	2 x 18 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	500
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	24
<b>P (NO. OF POLES)</b>	2
<b>Height (Height / mm)</b>	17
<b>Width (Width / mm)</b>	20
<b>Depth (Depth / mm)</b>	27.3
<b>COLOR (COLOR)</b>	weiß
<b>Comment (Comment)</b>	ohne Aufdruck