

IMMERSION PUMP POWER

High performance immersion pump for high requirements

POWER Pump 22 litre

Art. Nr. 088 Power pump

Art. Nr. 08 Power Pump with check valve

TECNICAL SPECIFICATIONS:

- 1.- 12 V direct-current voltage 3,7-4,2 A
- 2.- Discharge flow max. 22 l/m
- 3.- Pressure height max. 14 m (1,4 bar)
- 4.- Independent rotating direction 5-P- Motor
- 5.- dry-running seals with lifetime lubrication and ventilation
- 6.- Easy to clean dirt filter on the absorption side
- 7.- Suitable for 10mm diameter hose connector
- 8.- Dimension: diameter 80mm x length 135 mm, weight 290g, 1 m cable length.