


**HEADER RIGHT ANGLE SOLDER PIN  
0.8x0.8 MM WITH THREADED  
FLANGES PIN SPACING 3.5 MM / 0.  
138 IN 100% PROTECTED AGAINST**



**HEADER RIGHT ANGLE SOLDER PIN  
0.8x0.8 MM WITH THREADED  
FLANGES PIN SPACING 3.5 MM / 0.  
138 IN 100% PROTECTED AGAINST  
MISMATING  
713-1423/117-000 TO 713-1438/117-000**

<b>ITEM-NO. (ITEM-NO.)</b>	713-1428/117-000
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	16
<b>Height (Height / mm)</b>	13.3
<b>Width (Width / mm)</b>	38.1
<b>Depth (Depth / mm)</b>	13.5
<b>No. of connection Points (No. of connection Points)</b>	16
<b>No. of potentials (No. of potentials)</b>	16
<b>COLOR (COLOR)</b>	schwarz
<b>Comment (Comment)</b>	$L = ((\text{No. of poles} / 2) - 1) \times \text{Pin Spacing} + 13.6 \text{ mm}$
<b>Dimensions (Dimensions)</b>	1.2 +0.1 mm