



**FEMALE PLUG WITH LOCKING  
LEVER PIN SPACING 5 MM / 0.197 IN  
100% PROTECTED AGAINST  
MISMATING**

721-102/037-000 TO 721-120/037-000

ITEM-NO. (ITEM-NO.)	721-108/037-000
Cross section1 (Cross section / mm <sup>2</sup> )	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	8
Height (Height / mm)	14.3
Width (Width / mm)	56.6
Depth (Depth / mm)	29.6
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	8
COLOR (COLOR)	lichtgrau
Comment (Comment)	L = (No. of poles x Pin Spacing)