



**ANGLED FEMALE PLUG WITH FIXING
FLANGE PIN SPACING 5 MM / 0.197 IN
100% PROTECTED AGAINST
MISMATING**

721-106/027-000 TO 721-120/027-000

ITEM-NO. (ITEM-NO.)	721-112/027-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	12
Height (Height / mm)	14.3
Width (Width / mm)	74.8
Depth (Depth / mm)	26.45
No. of connection Points (No. of connection Points)	12
No. of potentials (No. of potentials)	12
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	26.1
Comment (Comment)	L1 = (No. of poles x Pin Spacing) + 3 mm L2 = (No. of poles x Pin Spacing) + 8,8 mm L3 = (No. of poles x Pin Spacing) + 14,8 mm