



**MALE CONNECTOR WITH STRAIGHT
LONG CONTACT PINS PIN SPACING 5
MM / 0.197 IN 100% PROTECTED
AGAINST MISMATING**
721-162/003-000 TO 721-180/003-000

ITEM-NO. (ITEM-NO.)	721-162/003-000
Measured voltage (Measured voltage / V)	250
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	2
Height (Height / mm)	12
Width (Width / mm)	13.2
Depth (Depth / mm)	11.4
COLOR (COLOR)	lichtgrau
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm