



**MALE CONNECTOR WITH STRAIGHT  
LONG CONTACT PINS PIN SPACING 5  
MM / 0.197 IN 100% PROTECTED  
AGAINST MISMATING**  
721-162/003-000 TO 721-180/003-000

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 721-165/003-000                           |
| <b>Measured voltage (Measured voltage / V)</b>              | 250                                       |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4   |
| <b>Pollution degree (Pollution degree)</b>                  | 3   |
| <b>Current intensity (Current intensity / A)</b>            | 16  |
| <b>RM (PIN SPACING / mm)</b>                                | 5   |
| <b>P (NO. OF POLES)</b>                                     | 5   |
| <b>Height (Height / mm)</b>                                 | 12  |
| <b>Width (Width / mm)</b>                                   | 28.2                                      |
| <b>Depth (Depth / mm)</b>                                   | 11.4                                      |
| <b>COLOR (COLOR)</b>  | lichtgrau                                 |
| <b>Comment (Comment)</b>                                    | A = (No. of poles x Pin Spacing) + 3,2 mm |