



**MALE CONNECTOR WITH STRAIGHT  
LONG CONTACT PINS PIN SPACING 5  
MM / 0.197 IN 100% PROTECTED  
AGAINST MISMATING**  
721-162/003-000 TO 721-180/003-000

|  |   |
|--|---|
| ITEM-NO. (ITEM-NO.)                                  | 721-174/003-000                           |
| Measured voltage (Measured voltage / V)              | 250                                       |
| Measured shock voltage (Measured shock voltage / kV) | 4   |
| Pollution degree (Pollution degree)                  | 3   |
| Current intensity (Current intensity / A)            | 16  |
| RM (PIN SPACING / mm)                                | 5   |
| P (NO. OF POLES)                                     | 14  |
| Height (Height / mm)                                 | 12  |
| Width (Width / mm)                                   | 73.2                                      |
| Depth (Depth / mm)                                   | 11.4                                      |
| COLOR (COLOR)  | lichtgrau                                 |
| Comment (Comment)                                    | A = (No. of poles x Pin Spacing) + 3,2 mm |