



**ANGLED FEMALE PLUG WITH FIXING
FLANGE PIN SPACING 7.5 MM / 0.295
IN 100% PROTECTED AGAINST
MISMATING**

721-206/027-000 TO 721-212/027-000

ITEM-NO. (ITEM-NO.)	721-206/027-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	6
Height (Height / mm)	14.3
Width (Width / mm)	57.3
Depth (Depth / mm)	26.45
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	6
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	13.49
Comment (Comment)	A= (No. of poles - 1) x Pin Spacing L1 = A + 5 mm + 3 mm L2 = A + 5 mm + 8,8 mm L3 = A + 5 mm + 14,8 mm