



**FEMALE PLUG WITH LOCKING
LEVER PIN SPACING 7.5 MM / 0.295 IN
100% PROTECTED AGAINST
MISMATING**

721-202/037-000 TO 721-212/037-000

ITEM-NO. (ITEM-NO.)	721-211/037-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	11
Height (Height / mm)	14.3
Width (Width / mm)	96.6
Depth (Depth / mm)	29.6
No. of connection Points (No. of connection Points)	11
No. of potentials (No. of potentials)	11
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	
Comment (Comment)	$L = (\text{No. of poles} - 1) \times \text{Pin Spacing} + 5 \text{ mm}$