





**2-CONDUCTOR SPRING CLAMPS PIN
SPACING 7,5 mm / 0.295 IN 100%
PROTECTED AGAINST MISMATING
721-2202/026-000 TO 721-2212/026-000**

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	721-2209/026-000
Cross section1 (Cross section / mm²)	0.2 - 2.5
Cross section2 (Cross section / AWG)	24 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	9
Height (Height / mm)	20.8
Width (Width / mm)	65
Depth (Depth / mm)	29.8
No. of connection Points (No. of connection Points)	18
No. of potentials (No. of potentials)	9
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	25.367
Comment (Comment)	L = (No. of poles - 2) x Pin Spacing + 12,5 mm