





**2-CONDUCTOR SPRING CLAMPS
WITH LOCKING LEVER PIN SPACING
7.5 MM / 0.295 IN
721-2202/037-000 TO 721-2212/037-000**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 721-2212/037-000 |
| Cross section1 (Cross section / mm²) | 0.2 - 2.5 |
| Cross section2 (Cross section / AWG) | 24 - 12 |
| Strip length (Strip length / mm) | 9 - 10 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 16 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 12 |
| Height (Height / mm) | 20.8 |
| Width (Width / mm) | 87.5 |
| Depth (Depth / mm) | 26.45 |
| No. of connection Points (No. of connection Points) | 24 |
| No. of potentials (No. of potentials) | 12 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 34.016 |
| Comment (Comment) | L = (No. of poles - 2) x Pin Spacing + 12,5 mm |